

U22REX/P-SL H1659-08

U22REX/P-SL is a 8" High Fidelity woofer with an injection moulded metal chassis, intended for bass reflex and transmission line designs.


New Curv cone, a woven polypropylene with excellent internal damping together with perfectly matched moving parts gives a smooth, extended frequency response.


Bumped back plate in the magnet system together with a high temperature voice coil wound on an aluminium voice coil former gives low distortion and high power handling capacity. Heavy copper ring below the T-shaped pole piece will reduce non linear and modulation distortion.

Bullet shaped phase plug reduces compression due to temperature variations in the voice coil, avoids resonance problems which would occur in the volume between the dust cap and the pole piece and increases the long term power handling capacity.

Extremely stiff and stable injection moulded metal basket, keeps the critical components in perfect alignment. Large windows in the basket both above and below the spider reduce sound reflection, air flow noise and cavity resonance to a minimum.







The frequency responses above show measured free field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. Input the frequency responses above show measured free field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. Input the frequency responses above show measured free field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. Input the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees angle using a 21L closed box. In put the field sound pressure in 0, 30, and 60 degrees and 60 degree and 60 degree and 60 degree and 60 degree and 602.83 VRMs, microphone distance 0.5m, normalized to SPL 1m. The dotted line is a calculated response in infinite baffle based on the parameters given for this specific driver. The impedance is measured in free air without baffle using a 2V

Nominal Impedance	8 Ohms	Voice Coil Resistance	6.0 Ohms
Recommended Frequency Range	29 - 4000 Hz	Voice Coil Inductance	0.7 mH
Short Term Power Handling *	250 W	Force Factor	8.0 N/A
Long Term Power Handling *	100 W	Free Air Resonance	29 Hz
Characteristic Sensitivity (2,83V, 1m)	90.5 dB	Moving Mass	19.8 g
Voice Coil Diameter	39 mm	Air Load Mass In IEC Baffle	1.9 g
Voice Coil Height	14 mm	Suspension Compliance	1.7 mm/N
Air Gap Height	6 mm	Suspension Mechanical Resistance	2.1 Ns/m
Linear Coil Travel (p-p)	8 mm	Effective Piston Area	220 cm ²
Maximum Coil Travel (p-p)	20 mm	VAS	103 Litres
Magnetic Gap Flux Density	1.0 T	QMS	1.77
Magnet Weight	0.64 kg	QES	0.34
Total Weight	2.2 kg	QTS	0.29

*IEC 268-5 Oct 2012 SEAS reserves the right to change technical data

RoHS compliant product www.seas.no